



MEDI-TECH
SOLUTIONS

Velashape RF-Tight Vacuum Slimming Machine



F
A
S
T

S
E
R
V
I
C
E

A
N
D

B
E
S
T

V
A
L
U
E

CE



Van + Tight + Rollit + Rollr + IR

Vacuum + RF Tight + Roller + LED + IR

Handpiece 1 , Handpiece 2 , Handpiece 3

■ Application



Handpiece 1

1. Convenient Operation with handle button
2. 4 different rolling directions with multi-dimensional effects

Mainly for small area treatment. For slimming, body sculpting, cellulite removal etc.



Handpiece 2

1. High precision processed treatment head
2. Non-invasive delicate treatment for Face Carving

Face lifting, skin rejuvenation, wrinkle removal, anti-aging etc.




Handpiece 3

1. Head-to-toe targeted skin smoothing
2. Without downtime
3. Ergonomic hand piece while letting the system take care of delivering the right temperature

Optimizes treatment efficacy on the abdomen, flanks, buttocks, inner and outer thighs, upper arms, bra and back fat, as well as around the eyes, mouth, cheeks and

■ Principle

Synergy 360MMAX is a perfect combination of five technologies: vacuum, mechanical massage roller, infrared light, RF Tight ,LED light. It gives solution to skin laxity, wrinkle,fat accumulation and cellulite through tissue regeneration,non-invasive treatment, and then achieve the efffect of face lifting and body sculpturing.



■ Proven Clinical Results



Eyes Before
After 1

Face neck
Before After 1

Arm Slim
Before After 2



Cellulite Before
After 1

Cellulite Before
After 3


Cellulite Before
After 4

Top-to-toe: targeted skin smoothing



RF tight emits at a low 10MHz frequency to infiltrate deep down for deeper skin tissue Penetration

RF power to the target temperature very gradually and then maintains it, delivering precise heating to the skin's surface with predictable and consistent results.



360MMAX monitors skin tissue temperature and impedance in real time. It automatically adjusts the RF power for heat to penetrate deeper and more uniformly.



Wrinkle Reduction



Fat Reduction



Skin Tightening



The world only one who can achieve real effect on lifting the upper eyelid! Sculpture All your face.



Get you beautiful swan neck.



Remove mamma accessoria and reshape breast.



Give you perfect abdomen shape and lift your hip.



Remodel beautiful legs and remove cellulite.



Shape your calves with smooth skin, and say good-by to thick calves.



F A S T S E R V I C E A N D B E S T V A L U E

■ Advantages

USA Imported vacuum pump --- Express efficiency in silence




Ultra-quiet and Strong Suction, enjoy the comfortable and effective results.


Global Unique Updated Rollers Rotation Technology with four directions:
In, Out, Up, Down ----- Bring professional excellent results.

Roll in: fat elimination
Roll out: cellulite removal

Roll up: shaping
Roll down: body contouring



RF power ensures safety and perfect effects --- Enhance efficiency and comfort



1. Controllable penetration depth
2. Uniform energy distribution
3. Comfortable treatment, say no for tingling
4. 10MHz RF Power for body and face lift firming
5. uses temperature control technology, to ensure safety and efficacy

■ Technique Specification

Radio Frequency Power	Up to 50W
Focused Technology	Vacuum +RF Tight + Roller + LED + IR
Delivery Type	Pulse; CW
RF Frequency	10MHz
Pump Suction Rate	25cub.m/h
Infrared Lamp	Up to 20W
Light Spectrum	640nm (infrared); 690nm (LED)
Handpiece	1×Vacuum+RF (34.5x48mm) 1×Vacuum+RF (18x25mm) 1×RF Tight(8.5x15mm)
Cooling	Self-contained
Display	10.4" True Color LCD Touch Screen
Electrical Requirements	220V±10% 50/60Hz, 110V±10% 50/60Hz
Net Weight	25 KG
Dimensions (WxLxH)	57.5*56*63cm